


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	RELEASED	08/10/09	DFP





NOTE:

THIS KIT CONTAINS ONE EACH OF THE FOLLOWING ADAPTERS;

- BNC FEMALE TO DUAL BINDING POSTS
- BNC MALE TO DUAL BINDING POSTS
- BNC FEMALE TO DUAL BANANA PLUGS
- BNC MALE TO BNC MALE
- BNC FEMALE TO BNC FEMALE

SEVEN COMPARTMENT PLASTIC BOX (TWO SPARE COMPARTMENTS)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 / -0 > 120 [3048] ≤ 300 [7620] = +6 / -0 > 300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± 0.2 .XX = ± 0.02 .XXX = ± 0.005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY D. PARHAM	08/10/2009		CATEGORY COAXIAL		
	CHECKED BY D. FRISIELLO	08/10/2009				
	APPROVED BY D. CASTRO	08/10/2009	PRODUCT DESCRIPTION KIT ADAP BNC M/F - DUAL BANANA			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. BC2700K	REV. A
SCALE: 1:2		CAD FILE: BC2700K.SLDRW		SHEET 1 OF 1		