


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 7318: RE-MODEL ADAPTER, REVISE FORMAT, NOTES, ROHS	2/28/14	D.FRISIELLO



**NOTES:**

1. WIRED STRAIGHT THROUGH FROM PIN TO LIKE-NUMBERED PIN.
2. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

**MATERIAL:**

ADAPTER HOUSING: PVC, LIGHT GRAY

**FINISH:**

CONNECTOR PINS: MATING SURFACES: GOLD FLASH.

**PACKAGING:**

ADAPTER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**

CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5.08] .XX = $\pm .02$ [51] .XXX = $\pm .005$ [1.27]	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY TJC	2/12/02			
	CHECKED BY D PARHAM	2/13/2002	CATEGORY	HETEROGENEOUS	
	APPROVED BY C McCORMICK	2/13/2002	PRODUCT DESCRIPTION	CN50M TO HPDB50F SCSI ADAPTER	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CAA910MF</b>	REV. <b>E</b>
REF	SCALE: NONE	CAD FILE: CAA910MF.SLDRW	SHEET 1 OF 1		