





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/25/2022	GUTTADAURO

D
C
B
A

D
C
B
A





DETAIL A

DETAIL C

NOTES:

- VOLTAGE RATING:
DIELECTRIC VOLTAGE WITHSTAND TEST: 2000V/1 SECOND
CONDUCTOR RESISTANCE: ≤22.4 Ω/1000 METERS
VOLTAGE RATING: AC 300/500V
- CABLE MARKING:
CCC A133679 60227 IEC 53 (RVV) 300/500V 3×0.75MM².
- OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
- CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.
- ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY AKRESOWSK	04/22/2022	
OVERALL CABLE LENGTH TOLERANCES:	CHECKED BY DGUST	04/22/2022	CATEGORY
≤12 [305] = +1 [25] / -0	APPROVED BY GUTTADAURO	04/22/2022	POWER PRODUCTS
>12 [305] ≤60 [1524] = +2 [51] / -0			PRODUCT DESCRIPTION
>60 [1524] ≤120 [3048] = +4 [102] / -0			CABLE ASSY, INTL PWR, TYPE I RT-ANG TO C13 RT-ANG, 10A, 2M
>120 [3048] ≤300 [7620] = +6 [152] / -0			SIZE
>300 [7620] = +5% / -0			A
ALL OTHER DIMENSIONAL TOLERANCES:	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CAGE CODE
.X = ±.2 [5] FRACTIONS ± 1/32	COLOR VARIATIONS MAY OCCUR		43321
.XX = ±.02 [5] ANGLES ±1°			ITEM NO.
.XXX = ±.005 [13]			CPCIDC13R-10A-2M
THIRD-ANGLE PROJECTION			REV.
			A
			SCALE: NONE
			CAD FILE: CPCIDC13R-10A-2M.SLDDRW
			SHEET 1 OF 1

8 7 6 5 4 3 2 1