


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/14/14	D.GRIFFIN
A	ECN 99999: UPDATED TO CORRECT ORIENTATION OF LOGO ON MALE END	1/13/16	S.LI




"P1"  
5-PIN MICRO B PLUG  
CONTACTS: 30 μINCHES  
GOLD PLATING



ONE 28AWG STRANDED TINNED COPPER TWISTED PAIR  
THREE 28AWG STRANDED TINNED COPPER CONDUCTORS  
OVERALL ALUMINIZED POLYESTER SHIELD WITH DRAIN WIRE  
PLUS TINNED COPPER BRAIDED SHIELD.  
PVC OUTER JACKET, BLACK

"J1"  
5-PIN MICRO-B FEMALE  
CONTACTS: 30 μINCHES  
GOLD PLATING

MODEL NUMBER	LENGTH METERS [FEET]
CSMUMICBX-03M	0.3 [.98]
CSMUMICBX-05M	0.5 [1.64]
CSMUMICBX-075M	0.75 [2.46]
CSMUMICBX-1M	1.0 [3.28]
CSMUMICBX-2M	2.0 [6.56]
CSMUMICBX-3M	3.0 [9.84]



**NOTES:**

1. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**

CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY D.FRISIELLO	11/11/13				
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY R.SCOTT	11/11/13	CATEGORY USB			
	APPROVED BY S. SMITH	11/11/13	PRODUCT DESCRIPTION CA USB MICRO B M/F EXT			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. CSMUMICBX	REV. <b>A</b>
SCALE: NONE			CAD FILE: CSMUMICBX.SLDDRW		SHEET 1 OF 1	