


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION BY D. DOLCE	2/11/02	DFP
B	PRODUCT VALIDATION UPDATE (ECN 1204)	12/12/02	MCCORMICK
C	ECN 3255: REVISED MOLDED BOOTS AND CN RELEASE	3/27/08	D.FRISIELLO
D	ECN 5879: REMOVED UL STYLE 1792, NEW FORMAT REVISED NOTE 2	12/9/11	D.FRISIELLO



MODEL NUMBER	LENGTH	
	FEET	METERS
CTL1RB-1	1.0	.31
CTL1RB-5	5.0	1.52
CTL1RB-10	10.0	3.05
CTL1RB-15	15.0	4.57
CTL1RB-25	25.0	7.62

NOTES:

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D PARHAM	1/29/2002		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	CHECKED BY T CLARK	1/29/2002	CATEGORY COAXIAL	
	APPROVED BY R CARRICK	1/29/2002	PRODUCT DESCRIPTION CA RCA M/BNC M THIN LINE	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
	COLOR VARIATIONS MAY OCCUR		DWG. NO. CTL1RB	REV. D
	SCALE: NONE		CAD FILE: CTL1RB.SLDDRW	
			SHEET 1 OF 1	