


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
C	ECN 4686: CN RELEASE	13.APR.2010	Bill_Zhang



WIRING CHART	
HD15 M	BNC M
PIN1	P1
PIN2	P2
PIN3	P3
PIN4	N/C
PIN5	SHIELD
PIN6	SHIELD
PIN7	SHIELD
PIN8	SHIELD
PIN9	N/C
PIN10	SHIELD
PIN11	N/C
PIN12	N/C
PIN13	P4
PIN14	N/C
PIN15	N/C
SHELL	SHIELD

ALL BNC SHIELDS TIED TO SHELL

- NOTES
1. CABLES TO BE TESTED FOR CONTINUITY
  2. CABLES TO BE INDIVIDUALLY PACKAGED PER L-com PACKAGING SPECIFICATION PS-0031
  3. HD15 CONNECTOR DUST COVER INSTALLED FOR SHIPPING (NOT SHOWN)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: <math>\le 12 [305] = +1 [25] / -0</math> <math>> 12 [305] \le 60 [1524] = +2 [51] / -0</math> <math>> 60 [1524] \le 120 [3048] = +4 [102] / -0</math> <math>> 120 [3048] \le 300 [7620] = +6 [152] / -0</math> <math>> 300 [7620] = +3\% / -0\%</math>	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY <b>Bill_Zhang</b>	03/24-'10		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	CHECKED BY <b>Frank_Mao</b>	03/24-'10	CATEGORY <b>AUDIO/VIDEO</b>	
	APPROVED BY <b>Thomas_Lu</b>	03/24-'10	PRODUCT DESCRIPTION <b>CBL, HD15P M/4xBNC 75 OHM M W/FERRITE</b>	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
REF	SCALE: NONE	CAD FILE: CTL4CAT-6F.SLDDRW	DWG. NO. <b>CTL4CAT-6F</b>	REV. <b>C</b>