


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
C	ECN 4686: CN RELEASE	13.APR.2010	Bill_Zhang



WIRING CHART	
HD15 M	BNC M
PIN1	P1
PIN2	P2
PIN3	P3
PIN4	N/C
PIN5	SHIELD
PIN6	SHIELD
PIN7	SHIELD
PIN8	SHIELD
PIN9	N/C
PIN10	SHIELD
PIN11	N/C
PIN12	N/C
PIN13	P4
PIN14	N/C
PIN15	N/C
SHELL	SHIELD

PART NUMBER	LENGTH FEET [METERS]
CTL4CAT-3	3.0 [.91]
CTL4CAT-6	6.0 [1.82]

- NOTES**
- CABLES TO BE TESTED FOR CONTINUITY.
 - CABLES TO BE INDIVIDUALLY PACKAGED PER L-com PACKAGING SPECIFICATION PS-0031.
 - HD15 CONNECTOR DUST COVER INSTALLED FOR SHIPPING (NOT SHOWN).

ALL BNC SHIELDS TIED TO SHELL

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY Bill_Zhang	04/07-'10		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY Frank_Mao	04/07-'10	CATEGORY AUDIO/VIDEO	
	APPROVED BY Thomas_Lu	04/07-'10	PRODUCT DESCRIPTION CA VGA BKT HD15 M/4 BNC M	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE A	FSCM NO. 43321	DWG. NO. CTL4CAT
REF	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: CTL4CAT.SLDDRW	SHEET 1 OF 1