



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 4845: CN RELEASE	22.APR.2010	Bill_Zhang



WIRING CHART	
HD 15P F	BNC F
PIN 1	J1
PIN 2	J2
PIN 3	J3
PIN 4	N/C
PIN 5	SHIELD
PIN 6	SHIELD
PIN 7	SHIELD
PIN 8	SHIELD
PIN 9	N/C
PIN 10	SHIELD
PIN 11	N/C
PIN 12	N/C
PIN 13	J5
PIN 14	J4
PIN 15	N/C
SHELL	SHIELD

ALL BNC SHIELDS TIED TO HD15P F SHELL

- NOTES:
1. CABLES TO BE TESTED FOR CONTINUITY.
  2. CABLES TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-com PACKAGING SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY <b>Bill_Zhang</b>	04/22-10		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY <b>Frank_Mao</b>	04/22-10	CATEGORY <b>AUDIO/VIDEO</b>	
	APPROVED BY <b>Dan_Castro</b>	05/13-10	PRODUCT DESCRIPTION <b>CA HD15 F to (5) BNC F</b>	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
			DWG. NO. <b>CTL5CAR-2T</b>	REV. <b>E</b>
			SCALE: NONE	CAD FILE: CTL5CAR-2T.SLDDRW
				SHEET 1 OF 1