


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

**RoHS Compliant** ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
C	ECN 3791: CN RELEASE	1/12/09	D.CASTRO
D	ECN 6519: UPDATED FORMAT, PACKAGING, AND LOGOS	11/19/12	D. DESJARDIN
E	ECN6725:REVISED DIMENSION 1.00 TO 1.0	03/12/13	B.ZHANG



WIRE MAP	
HD15 PLUG	BNC PLUG
PIN 1	P1
PIN 2	P2
PIN 3	P3
PIN 4	N/C
PIN 5	SHIELD
PIN 6	SHIELD
PIN 7	SHIELD
PIN 8	SHIELD
PIN 9	N/C
PIN 10	SHIELD
PIN 11	N/C
PIN 12	N/C
PIN 13	P5
PIN 14	P4
PIN 15	N/C
SHELL	SHIELD

MODEL NUMBER	LENGTH		COLOR: CABLE JACKET, MOLDED HOOD, MOLDED STRAIN RELIEFS, FERRITE OVERMOLD
	FEET	METER	
CTL5CAT-6F	6.0	1.83	GRAY (424C)
CTL5CAT-6BF	6.0	1.83	BLACK

NOTES: ALL BNC SHIELDS TIED TO SHELL

1. CABLE SHALL BE TESTED FOR CONTINUITY.
2. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY BILL_ZHANG	10/20/08		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY FRANK_MAO	10/20/08	PRODUCT DESCRIPTION	
PROJECTION	APPROVED BY THOMAS_LU	10/20/08	CA VGA BKT HD15 M/5 BNC M	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE	FSCM NO.
	COLOR VARIATIONS MAY OCCUR		A	43321
			DWG. NO.	CTL5CAT-6F
			REV.	E
			SCALE: NONE	CAD FILE: CTL5CAT-6F.SLDDRW
				SHEET 1 OF 1