


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/29/2020	GUTTADAURO





ITEM NUMBER	TYPE	DATA RATE	CONNECTOR TYPE	CABLE TYPE	CODING	LENGTH	
DAC-P10GMSA-05M	PASSIVE	10GIG	SFP+	TWINAX	MSA	1.64ft	0.5m
DAC-P10GMSA-1M	PASSIVE	10GIG	SFP+	TWINAX	MSA	3.28ft	1m
DAC-P10GMSA-105M	PASSIVE	10GIG	SFP+	TWINAX	MSA	4.92ft	1.5m
DAC-P10GMSA-2M	PASSIVE	10GIG	SFP+	TWINAX	MSA	6.56ft	2m
DAC-P10GMSA-3M	PASSIVE	10GIG	SFP+	TWINAX	MSA	9.84ft	3m
DAC-P10GMSA-4M	PASSIVE	10GIG	SFP+	TWINAX	MSA	13.12ft	4m
DAC-P10GMSA-5M	PASSIVE	10GIG	SFP+	TWINAX	MSA	16.40ft	5m
DAC-P10GMSA-6M	PASSIVE	10GIG	SFP+	TWINAX	MSA	19.69ft	6m
DAC-P10GMSA-7M	PASSIVE	10GIG	SFP+	TWINAX	MSA	22.97ft	7m

NOTES:

- 1a. STORAGE TEMP: -40°C MIN TO +85°C MAX.
- 1b. OPERATING CASE TEMP: -5°C MIN TO +75°C MAX.
- 1c. WATTAGE: 0.35W.
- 1d. POWER SUPPLY VOLTAGE (Vcc): 3.14V MIN, 3.3V TYP., 3.47V MAX.
- 1e. POWER SUPPLY CURRENT (Icc) 100mA.
- 1f. TOTAL POWER CONSUMPTION(Pd): 0.5W.

2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DZINN	06/29/2020	
CHECKED BY DFRISIELLO	06/29/2020	PRODUCT DESCRIPTION DAC Cable, Passive, 10Gig, SFP+/SFP+, MSA	
APPROVED BY GUTTADAURO	06/29/2020		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR
THIRD-ANGLE PROJECTION 	SIZE A	CAGE CODE 43321	ITEM NO. DAC-P10GMSA
SCALE: NONE		CAD FILE: DAC-P10GMSA.SLDDRW	
SHEET 1 OF 1			REV. A