



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES DHP9G-OD1	08/23/2012	DFRISIELLO
B	ECN 10590: REVISED 3D MODEL AND DRAWING	08/11/2020	BGATES



B

NOTES:

- ENCLOSURE IS ABS PLASTIC COLOR: DARK GRAY.
- COVER HALVES SNAP TOGETHER TO RETAIN CONNECTORS AND CAPTIVE HARDWARE.
- HOUSING ACCEPTS STANDARD 9 POSITION D-SUB OR 15 POSITION, HIGH DENSITY CONNECTORS (NOT SUPPLIED).
- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- COMPONENT ASSEMBLY IS SHIPPED UN-ASSEMBLED.
- JUMPER WIRES ARE SUPPLIED SEPARATELY.
- COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [5]      ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY D.PARHAM CHECKED BY C.MCCORMICK APPROVED BY R.CARRICK	05/30/2003 06/02/2003 06/02/2003	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION ADPT, COVER DB9 GRAY PLASTIC	SIZE <b>A</b>
CAGE CODE <b>43321</b>		ITEM NO. <b>DHP9G</b>	REV. <b>B</b>
SCALE: NONE		CAD FILE: DHP9G.SLDDRW	SHEET 1 OF 1