


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED TO PRODUCTION	11/14/00	R.CARRICK
B	REVISED THUMB SCREWS PER ECO # 0829	01/15/01	MCCORMICK
C	ECN 3370: REMOVE PANTONE 2945 BLUE/TEXT COLOR WHITE FROM NOTE 7	6/6/08	D.GRIFFIN
D	ECN5138: REMOVE LABEL REQUIREMENTS. ADDED PKG NOTE. UPDATED FORMAT.	11/12/10	DFP

2X 4-40 UNC-2A THREAD





25 PIN MALE
D-SUB
CONNECTOR

WIRE DIAGRAM	
DB25M	DB25M
PIN 4	PIN 15
PIN 5	PIN 17
PIN 6	PIN 13
PIN 7	PIN 12
PIN 8	PIN 10
PIN 9	PIN 11

NOTES:

1. ALL- METAL HOUSING PROVIDES 100% SHIELDING.
2. CONNECTOR CONTACTS PLATING; GOLD FLASH.
3. INSULATOR MATERIAL; GLASS FILLED PBT U.L. RECOGNIZED 94V-0 RATED.
4. LOOPBACK ADAPTOR USES PINS IN WIRE DIAGRAM ONLY.
5. JACKSCREW PLATING; NICKEL PLATED.
6. ALL OTHER METAL COMPONENTS PLATING; TIN PLATED.
7. ADAPTOR TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
8. DRAWING SUPERSEDES DRAWING #96-060102.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY RON CARRICK	10/4/2000	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	CHECKED BY TJC	10/23/2000	CATEGORY DATA CABLING
	APPROVED BY DFP	10/23/2000	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION ADPT, LOOPBACK PARALELL TEST DB25M	SIZE A FSCM NO. 43321 DWG. NO. DMA019S REV. D
	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: DMA019S.SLDDRW SHEET 1 OF 1