


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES DML009S-OD1	09/30/2014	D.DESJARDIN
B	ECN 11061: REVISED L-COM LOGO	04/01/2021	BGATES



NOTES:

MATERIALS:

SHELL: NICKEL PLATED, COLD ROLLED STEEL
 COVER: NICKEL PLATED, COLD ROLLED STEEL
 INSULATOR: PBT GLASS FIBER REINFORCED UL94-V0, BLACK

APPLICATION:



COVER FITS STANDARD 9-CONTACT OR HIGH DENSITY 15-CONTACT FEMALE D-SUBMINIATURE RECEPTACLE.

LABELING:

PANTONE 2945 BLUE. "L-COM" FONT MyriaMM REGULAR. "DB9/HD15 COVER" FONT ARIAL BOLD, TEXT HEIGHTS: .085" TEXT COLOR; WHITE.

MISCELLANEOUS:

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY P.LACLAIR CHECKED BY C.MCCORMICK APPROVED BY R.CARRICK	DATE 10/01/2002 10/01/2002 10/01/2002	 an INFINITI® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY D-SUBMINIATURE	PRODUCT DESCRIPTION COVER, FOR DB9F/HD15F SHLD