


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING NUMBER WAS 97-082902	8/25/09	D. CASTRO




WIRE MAP
(IN ACCORDANCE WITH STANDARD 10BASE-T PRACTICE)

JACK NO.	RJ45 PIN NO.	50 PIN CONNECTOR	JACK NO.	RJ45 PIN NO.	50 PIN CONNECTOR
1	1	26	7	1	38
	2	1		2	13
	3	27		3	39
	6	2		6	14
2	1	28	8	1	40
	2	3		2	15
	3	29		3	41
	6	4		6	16
3	1	30	9	1	42
	2	5		2	17
	3	31		3	43
	6	6		6	18
4	1	32	10	1	44
	2	7		2	19
	3	33		3	45
	6	8		6	20
5	1	34	11	1	46
	2	9		2	21
	3	35		3	47
	6	10		6	22
6	1	36	12	1	48
	2	11		2	23
	3	37		3	49
	6	12		6	24


NO CONNECTIONS TO TELCO CONTACTS 25 & 50

NOTES:

- HOUSING IS ABS PLASTIC, COLOR: GRAY.
- EACH CLUSTER BAR IS INDIVIDUALLY PACKAGED IN A PLASTIC BAG WITH (2) 35mm (1.38) LONG WOOD SCREWS AND (1) PIECE OF DOUBLE SIDED MOUNTING TAPE OF THE SAME LENGTH AS THE ABS HOUSING.
- EACH CLUSTER BAR HAS A SPECIAL MOUNTING STRAP HAVING APPROXIMATELY 50mm OF VELCRO HOOKS AND 50mm OF FELT. THERE IS A PULL TAB ON THE HOOKS END AND A HEAT SEALED LOOP ON THE FELT END.



MODEL NUMBER	TELCO CONNECTOR
E412F10BASE-T	FEMALE
E412M10BASE-T	MALE



STRAP IS LOOPED THROUGH SLOT ON BRACKET OF THIS TELCO CONNECTOR AND HEAT SEALED

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY TJC CHECKED BY DFP APPROVED BY RC	DATE 9/29/97 9/11/00 9/11/00	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY MODULAR
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A FSCM NO. 43321 DWG. NO. E412M10BASE-T	PRODUCT DESCRIPTION CLSTR BAR 12PRT 10BASE-T/CN50
	SCALE: NONE		CAD FILE: E412M10BASE-T.SLDDRW	SHEET 1 OF 1