



8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/9/18	D.FRISIELLO



- NOTES:
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
 2. MATERIALS AND FINISH:
EXTERNAL PARTS: ALUMINUM/ELECTROLESS NICKEL, (BLACK)
MISCELLANEOUS HARDWARE: STAINLESS STEEL
SEAL: SILICONE / NITRILE
LANYARD: STAINLESS STEEL (NYLON COATED)
 3. USED WITH ECRP/ECSP STYLE IN-LINE RECEPTACLES
 4. COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION LSP-010-1.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY D.GUITADAURO APPROVED BY D.GUITADAURO	DATE 2/6/18 2/9/18 2/9/18	50 HIGH STREET NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY TELECOM/MODULAR
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION DCAP F+ LNYRD FOR RECP EN FINISH
	PROJECTION 	SIZE A	FSCM NO. 43321
SCALE: NONE		CAD FILE: ECRU5209U00.SLDDRW	
SHEET 1 OF 1			