


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASER	2/9/18	D.FRISIELLO



NOTES:

- CABLE RANGE: .190" / .270"
- ASSEMBLED OVERALL LENGTH IS APPROX. 3.3"
- MATERIALS AND FINISH:
EXTERNAL PARTS: ALUMINUM/ELECTROLESS NICKEL, (BLACK)
INTERNAL PARTS: ALUMINUM
MISCELLANEOUS HARDWARE: STAINLESS STEEL
SEAL: SILICONE
LANYARD: STAINLESS STEEL (NYLON COAT)
- LANYARD LENGTH: APPROXIMATELY 6.0"
- RATING: IP-68, WHEN MATED OR DUST CAP IS ENGAGED.
PERFORMANCE MEETS OR EXCEEDS CATEGORY 6 ANSI/EIA 568-C.2
- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- PARTS SHIPPED UNASSEMBLED.
- SUPPLIED PLUG FINISH, 50µIN GOLD OVER 100µIN NICKEL.
- COMPONENT SHALL BE INDIVIDUALLY PACKAGED
IN ACCORDANCE WITH L-COM SPECIFICATION LSP-010-1

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845				
	DRAWN BY D.FRISIELLO	2/6/18					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	CHECKED BY D.GUITADAURO	2/9/18	CATEGORY TELECOM/MODULAR				
	APPROVED BY D.GUITADAURO	2/9/18	PRODUCT DESCRIPTION C6 PLUG EN .190-.270 W/DUST CAP				
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	<table border="1"> <tr> <td>SIZE A</td> <td>FSCM NO. 43321</td> <td>DWG. NO. ECSA4219UA0</td> <td>REV. A</td> </tr> </table>	SIZE A	FSCM NO. 43321	DWG. NO. ECSA4219UA0	REV. A
SIZE A	FSCM NO. 43321	DWG. NO. ECSA4219UA0	REV. A				
SCALE: NONE		CAD FILE: ECSA4219UA0.SLDDRW	SHEET 1 OF 1				