


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



| REVISIONS | | | |
|-----------|-----------------|------------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 09/28/2021 | PHOSPODAR |
| | | | |
| | | | |



| PART NUMBER | LENGTH METER [FEET] |
|---------------------|---------------------|
| FCA-S2SR-SCASTU-01M | 1.0 [3.28] |
| FCA-S2SR-SCASTU-02M | 2.0 [6.56] |
| FCA-S2SR-SCASTU-03M | 3.0 [9.84] |
| FCA-S2SR-SCASTU-05M | 5.0 [16.40] |
| FCA-S2SR-SCASTU-10M | 10.0 [32.81] |
| FCA-S2SR-SCASTU-15M | 15.0 [49.21] |

NOTES:

- SC CONNECTOR ASSEMBLY POLISH TYPE: APC.
ST CONNECTOR ASSEMBLY POLISH TYPE: UPC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

| | | | | |
|--|---|--|---|---------------------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] | APPROVALS DRAWN BY: MVEERAPPAN CHECKED BY: DFRISIELLO APPROVED BY: PHOSPODAR | DATE 09/28/2021 09/28/2021 09/28/2021 |  an INFINITO brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 | |
| | THIRD-ANGLE PROJECTION  | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR | | CATEGORY FIBER OPTICS |
| SIZE A | | CAGE CODE 43321 | ITEM NO. FCA-S2SR-SCASTU | REV. A |
| SCALE: NONE | | CAD FILE: FCA-S2SR-SCASTU.SLDDRW | | SHEET 1 OF 1 |