


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/11/2022	PHOSPODAR



ASSY CONNECTIVITY	
AARC 2 CORE SKT	LC/PC
PIN1	B
PIN2	A



ITEM NO.	LENGTH	
	METER	FEET
FOC02B6027N01M	1.0	3.28
FOC02B6027N02M	2.0	6.56
FOC02B6027N05M	5.0	16.40
FOC02B6027N10M	10.0	32.81
FOC02B6027N15M	15.0	49.21

NOTES:

1. LC CONNECTOR POLISH TYPE: PC.
2. AARC CONNECTOR COMES WITH DUST CAP INSTALLED.
3. LC CONNECTORS COME WITH DUST PLUG INSTALLED (NOT SHOWN).
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS	DATE	 an INFINITO® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DZINN	01/18/2022	
	APPROVED BY PHOSPODAR	01/18/2022	CATEGORY FIBER OPTIC
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION Fiber Optic, Outdoor patch cable, Duplex MMF(OM3), 2 core AARC(Socket) to dual clipped LC/PC with 7.0mm LSZH jacket	
	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321
		ITEM NO. FOC02B6027N	REV. A
		SCALE: NONE	CAD FILE: FOC02B6027N.SLDDRW
		SHEET 1 OF 1	