


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/30/2022	DGUITADAURO



P1
HDMI FM 19P PIN: G/F
SHELL: GOLD PLATED

P2
HDMI FM 19P PIN: G/F
SHELL: GOLD PLATED



PIN Assignment

P1 HDMI AF	P2 HDMI AF
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
10	10
11	11
12	12
13	13
14	14
17	17
19	19
15	15
16	16
18	18
Shell	Shell

PART NUMBER	LENGTH	
	FEET	METERS
HDMI-FF-L-1M	3.28	1.0 ± .03
HDMI-FF-L-3M	9.84	3.0 ± .03

- NOTES:**
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 an INFINITO® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY DMAY			8/25/2022
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [1.3]	CHECKED BY HBAKKE	8/30/2022	PRODUCT DESCRIPTION LOCKING HDMI FEMALE TO FEMALE, 4K, BLACK PVC CABLE WITH NYLON BRAID		
	APPROVED BY DGUITADAURO	8/30/2022		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. HDMI-FF-L	REV. A
SCALE: NONE		CAD FILE: HDMI-FF-L.SLDDRW		SHEET 1 OF 1	