



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/30/2022	DGUITADAURO



**P1**  
HDMI AM 19P PIN: G/F  
SHELL: GOLD PLATED

**PIN Assignment**  
P1 HDMI AM      P2 HDMI AF



(1/0.23BC\*1P+D1/0.23BC+AL/MY)\*5P+1/0.23BC\*4C+AL/MY  
+D1/0.23BC+B64/0.12AM  
JACKET: BLACK PVC OD: 6.0  
+BLACK THREE WIRE NYLON NET OD: 6.8±0.2mm

**P2**  
HDMI FM 19P PIN: G/F  
SHELL: GOLD PLATED

PART NUMBER	LENGTH	
	FEET	METERS
HDMI-MF-L-1M	3.28	1.0 ± .03
HDMI-MF-L-3M	9.84	3.0 ± .03

- NOTES:**
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [5]      ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS DRAWN BY: DMAY CHECKED BY: HBAKKE APPROVED BY: DGUITADAURO	DATE 8/25/2022 8/30/2022 8/30/2022	 an INFINITO brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY AUDIO/VIDEO