


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/29/2022	DGUITADAURO



P1
HDMI AM 19P
SHELL/PIN: GOLD PLATED

P2
HDMI AM 19P
SHELL/PIN: GOLD PLATED

(1/0.23BC*1P+D1/0.23BC+AL-FOIL)*5C+1/0.23BC*4C+AL-FOIL
+D1/0.23BC+B164#/0.12AL-MG
JACKET: BLACK PVC
OD:6.0+BLACK THREE WIRE NYLON NET OD:6.8±0.15mm



PART NUMBER	LENGTH	
	FEET	METERS
HDMI-MM-F-05M	1.64	0.5 ± .02
HDMI-MM-F-1M	3.28	1.0 ± .03
HDMI-MM-F-2M	6.56	2.0 ± .03
HDMI-MM-F-3M	9.84	3.0 ± .03

- NOTES:**
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS DRAWN BY: DMAY CHECKED BY: HBAKKE APPROVED BY: DGUITADAURO	DATE 8/18/2022 8/29/2022 8/29/2022	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY AUDIO/VIDEO	
	THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION HDMI 2.0 MALE TO MALE W/ FERRITES, 4K, BLACK PVC NYLON BRAIDED CABLE	SCALE: NONE CAD FILE: HDMI-MM-F.SLDDRW SHEET 1 OF 1
	SIZE A CAGE CODE 43321 ITEM NO. HDMI-MM-F REV. A			