

6

5

4

3

2

1

REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	PRELIMINARY RELEASE	11/27/2023	DFRISIELLO	GUTTADAURO

F



E

D

C

B

A

AC POWER INPUT
POWER CORD INCLUDED72.0 ± 1.18 [1830 ± 30]
POWER CABLE.37 ± 0.1
[9.5 ± 0.3]

GND — +Vcc

NOTES:

SPECIFICATIONS:

CABLE: UL268, 22AWG 2 CONDUCTOR
JACKET: PVC, BLACKINPUT: 100~240 Vac, SINGLE PHASE / 50-60 Hz / CURRENT: 0.58A MAX.
DC OUTPUT: 24V ± 5% / 0~1A / TOTAL POWER: 24W MAX.

EMI: CE / FCC, CLASS B

PROTECTION: OVP, SCP, OCP

TEMPERATURE RANGE: -20°C ~ +80°C

MISCELLANEOUS:

COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

LABEL

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
 X = ±.2 [5] FRACTIONS
 .XX = ±.02 [0.5] ± 1/32
 .XXX = ±.005 [0.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:
 ≤12 [305] = +1 [25] / -0
 >12 [305] ≤ 60 [1524] = +2 [51] / -0
 >60 [1524] ≤ 120 [3048] = +4 [102] / -0
 >120 [3048] ≤ 300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.
UN-DIMENSIONED NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINIT@ brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936

DESCRIPTION

USB 2.0 Ranger 2304PoE Optional Power Supply, 24V 1A DC
Output, 100-240VAC Input, 2.1mm (ID) Plug & IEC320-C7 2-pin
Connector, 21-00110

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DFRISIELLO	ICR2304-PS	A

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
SCALE	SHEET
NONE	1 OF 1

6

5

4

3

2

1