


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/25/2022	GUTTADAURO

D
C
B
A



- NOTES:
- VOLTAGE RATING:
DIELECTRIC VOLTAGE WITHSTAND TEST: 2000V/1 SECOND
CONDUCTOR RESISTANCE: ≤26.0 Ω/1000 METERS
VOLTAGE RATING: AC 300/500V
 - CABLE MARKING:
+ + + + KEMA-KEUR NF-USE 1345 IEMMEQU H05VV-F 3G 0.75MM² V-75
300/500V ORDINARY DUTY NSW17436 YFC BON-EAGLE.
 - OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
 - CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.
 - ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY AKRESOWSK	04/20/2022	
OVERALL CABLE LENGTH TOLERANCE:	CHECKED BY DGUST	04/20/2022	CATEGORY
≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	APPROVED BY GUTTADAURO	04/20/2022	POWER PRODUCTS
ALL OTHER DIMENSIONAL TOLERANCES:	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION
.X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	COLOR VARIATIONS MAY OCCUR	SIZE A	CABLE ASSY, INTL PWR, TYPE F RT-ANG TO C13, 10A, 2M
THIRD-ANGLE PROJECTION		CAGE CODE 43321	ITEM NO. IPCFDC13-10A-2M
		SCALE: NONE	CAD FILE: IPCFDC13-10A-2M.SLDDRW
			SHEET 1 OF 1

8 7 6 5 4 3 2 1