


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/14/14	D.GRIFFIN



TYPE CEE7/7
SPLASH PROOF
PLUG APPROVAL
MARKS



CABLE MARKING:
PATELEC-CEM IEMMEQU <HAR> H05BQF3G1.0mm² G-PUR +S+S+S
CABLE APPROVED PER HD22.1

EN60320 C13
CONNECTOR
APPROVAL MARK



NOTES:

- PLUG: TYPE CEE7/7 SPLASH PROOF, BLACK
- CORD: H05BQF3G1.0mm BLACK, PUR
OD: 7.0 +/- 0.2mm [ø.275 +/- .008]
- TEMPERATURE RANGE: -40°C TO +90°C [-40°F TO 194°F]
- CONNECTOR: EN60320 C13, BLACK
- APPROVALS: KEMA-ENEC
- RATING: 10A/250V
- COLOR CODING: BLUE, BROWN, GREEN/YELLOW
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
- REGULATORY COMPLIANCE:**
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.27]	APPROVALS D.FRISIELLO CHECKED BY E.LAMOTT APPROVED BY M.MARTINEZ	DATE 8/13/14 8/13/14 8/13/14	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY POWER PRODUCTS	
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION CEE7/7-C13 250V LSZH BLK	
	PROJECTION 	SIZE A	FSCM NO. 43321	DWG. NO. LCPWR-CEE7-Z-3M
SCALE: NONE		CAD FILE: LCPWR-CEE7-Z-3M.SLDDRW		SHEET 1 OF 1