


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/12/12	D.FRISIELLO




NOTES:

- ENCLOSURE: METAL
- NUMBER OF VGA OUTPUT: 2
- SIGNAL BANDWIDTH: 350MHz
- SIGNAL TYPE: VGA, SVGA, MULTI-SYNC
- LED INDICATORS: POWER (GREEN) x 1
ACTIVE (AMBER) x 1
- CABLE LENGTH: 65.0 METERS (210 FT) MAX.
- CONNECTOR INPUT: HDB15 MALE x 1
- CONNECTOR OUTPUT: HDB15 FEMALE x 2
- POWER CONSUMPTION (MAX): DC 5V, 200mA, NORMAL OPERATION
10mA, POWER-SAVING MODE

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	10/11/12		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D.DESJARDIN	10/11/12	PRODUCT DESCRIPTION	
PROJECTION	APPROVED BY S.SMITH	10/11/12	VIDEO SPLITTER 1/2	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. LCVS-12	REV. A
			SCALE: NONE	CAD FILE: LCVS-12.SLDDRW
				SHEET 1 OF 1