


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	Initial Release	10/20/10	B.Puchaski
B	ECN 5640: REMOVED (2) D-HOLES	8/1/11	D. CASTRO
C	ECN 8755: MOVE THREADED STAND-OFF TO RIGHT UPPER CORNER OF DOOR	5/11/2017	R.CLARK



NOTE:  
 1- MATERIAL: 14 GA HOT ROLLED STEEL, CONTINUOUS WELDED SEAMS.  
 2- FINISH: GRAY POLYESTER POWDER COATING ( ANSI/ASA61 )  
 3- NEMA RATED TYPE 3, 3R, 3S, 4, 4X, 12 AND 13 PRIOR TO MODIFICATIONS.  
 4- UL 508 LISTED / CSA CERTIFIED.  
 5- TEMPERATURE RANGE FROM -50 DEG C TO 150 DEG C.  
 6- CABINETS ARE MAINTENANCE FREE AND CORROSION RESISTANT.  
 7- SHALL BE PACKAGED AS PER L-COM SPEC PKG-00070

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY B.Puchaski	10/20/10		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.3]	CHECKED BY K.Blomgren	10/20/10	PRODUCT DESCRIPTION NEMA Enclosure 14 x 12 x 6 Weatherproof 120VAC	
	APPROVED BY K.Blomgren	10/20/10	SIZE <b>A</b>	FSCM NO. <b>43321</b>
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	DWG. NO. NBS141206-100	REV. <b>C</b>
			SCALE: NONE	CAD FILE: NBS141206-100.SLDDRW
			SHEET 1 OF 1	