



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/03/10	B.PUCHASKI
B	ECN 5559 ADDED NOTE FOR PLATE AND HARDWARE	06/20/11	D.FRISIELLO
C	ECN 7940 UPDATE DRAWING	05/07/15	B.PUCHASKI
D	ECN 9060 LID GROUND STUD MOVED TO OPPOSITE SIDE	01/25/18	B.PUCHASKI



NOTE:
 1- MATERIAL: 14 GA HOT ROLLED STEEL, CONTINUOUS WELDED SEAMS.
 2- FINISH: GRAY POLYESTER POWDER COATING (ANSI/ASA61)
 3- NEMA RATED TYPE 3, 3R, 3S, 4, 4X, 12 AND 13 PRIOR TO MODIFICATIONS.
 4- UL 508 LISTED / CSA CERTIFIED.
 5- TEMPERATURE RANGE FROM -50 DEG C TO 150 DEG C.
 6- CABINETS ARE MAINTENANCE FREE AND CORROSION RESISTANT.
 7- SHALL BE PACKAGED AS PER L-COM SPEC PKG-00070
REGULATORY COMPLIANCE:
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ±.1 [2.54] .XX = ±.01 [25] .XXX = ±.005 [13] ANGULAR TOLERANCES: ALL = ± 1° PROJECTION 	APPROVALS B.PUCHASKI	DATE 05/03/10	 50 HIGH STREET NORTH ANDOVER, MA 01845	
	CHECKED BY M.AUDAS	DATE 05/03/10		CATEGORY ENCLOSURE
	APPROVED BY M.AUDAS	DATE 05/03/10	PRODUCT DESCRIPTION NEMA ENCLOSURE 14 X 12 X 6 WEATHERPROOF, STEEL	
	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321
		DWG. NO. NBS141206		
		SCALE: NONE	CAD FILE: NBS141206.SLDDRW	
		SHEET 1 OF 1		