


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 7198: ADDED +/-2% TOLERANCE, REVISED ROHS, FORMAT	12/16/13	D.FRISIELLO



VIIG "SCHUKO"
COLOR: BLACK
MINIMUM MARKINGS: KEMA, S

H05VVF3G1.0mm
MINIMUM MARKINGS: VDE
COLOR: BLACK

IEC320 C13
COLOR: BLACK

BAG LABEL EXAMPLE

PN: PCM1020

NOTES:

1. RATED 10A/250V.
2. LOW LEAD CONTENT 300ppm.
3. CONTINENTAL EUROPEAN CORD SET.
4. CORD TO BE PLACED IN A CLEAR BAG WITH WHITE LABEL: "PN: PCM1020"
5. CENTER THE LABEL ON THE CLEAR BAG.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.13]	APPROVALS DRAWN BY M.LAHEY CHECKED BY C.MCCORMICK APPROVED BY R.CARRICK	DATE 11/03/04 11/03/04 11/03/04		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY POWER PRODUCTS		
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION POWER CORD SCHUKO TO C13		
	PROJECTION 	SCALE: NONE	FSCM NO. 43321	DWG. NO. PCM1020	REV. E