


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|------------------------|------------|------------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | REV A DRAWING RELEASED | 11/16/2018 | DFRISIELLO |
| | | | |
| | | | |



NOTES:

1. MATERIAL: .06 THICK COLD ROLLED STEEL.
2. PANEL FINISH: FLAT BLACK POWDER COAT.
3. SILKSCREEN COLOR: WHITE.
4. PANEL SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.

| | | | | | | |
|--|-------------------------------------|--|--|--|--------------------------|------------------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3] | APPROVALS DRAWN BY DFRISIELLO | DATE 11/13/2018 | | 50 HIGH STREET NORTH ANDOVER, MA 01845 | | |
| | CHECKED BY MMARTINEZ | DATE 11/13/2018 | | CATEGORY RACK PANELS | | |
| | APPROVED BY MMARTINEZ | DATE 11/13/2018 | PRODUCT DESCRIPTION PNL,1U RACK w/16 .630"+CM BLK | | | |
| | PROJECTION | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | COLOR VARIATIONS MAY OCCUR | SIZE A | FSCM NO. 43321 | DWG. NO. PR175D16-630-CMB |
| SCALE: NONE | | | CAD FILE: PR175D16-630-CMB.SLDDRW | | SHEET 1 OF 1 | |