


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/10/17	J.LABOY



**NOTES:**

- MATERIAL: .06 THICK COLD ROLLED STEEL.
- PANEL FINISH: FLAT BLACK POWDER COAT.
- SILKSCREEN COLOR: WHITE.
- PANEL ASSEMBLY SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.

**REGULATORY COMPLIANCE:**  
CE 2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845		
	DRAWN BY B.PUCHASKI	05/02/17		CATEGORY	RACK/ENCLOSURE	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY D.FRISIELLO	05/08/17	PRODUCT DESCRIPTION	2U PNL W/32 CAT6 MINI COUPLERS		
	APPROVED BY M.MARTINEZ	05/02/17			<table border="1"> <tr> <td>SIZE <b>A</b></td> <td>FSCM NO. <b>43321</b></td> <td>DWG. NO. <b>PR35F504B-C6M</b></td> <td>REV. <b>A</b></td> </tr> </table>	SIZE <b>A</b>
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>PR35F504B-C6M</b>	REV. <b>A</b>			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SCALE: NONE			
COLOR VARIATIONS MAY OCCUR	CAD FILE: PR35F504B-C6M.SLDRW		SHEET 1 OF 1			