


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED FOR PRODUCTION		R.CARRICK
B	ECN#2620 UPDATE FORMATS, ADD METRIC DIMENSIONS, UPDATE NOTES	11/09/06	MCCORMICK
C	ECN 5376; RE-MODELED AND RE-DIMENSIONED	3/18/11	D.FRISIELLO



- NOTES:
1. MATERIAL: .06 THICK COLD ROLLED STEEL.
  2. PANEL FINISH: FLAT BLACK POWDER COAT.
  3. SILKSCREEN COLOR: WHITE.
  4. PANEL ASSEMBLY SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.
  5. PANEL ASSEMBLY IS SHIPPED WITH DUST CAPS INSTALLED. (NOT SHOWN)

**RoHS Compliant** ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  
 OVERALL CABLE LENGTH TOLERANCE:  
 ≤12 [305] = +1 [25] / -0  
 >12 [305] ≤60 [1524] = +2[51] / -0  
 >60 [1524] ≤120 [3048] = +4 [102] / -0  
 >120 [3048] ≤300 [7620] = +6 [152] / -0  
 >300 [7620] = +5% / -0%  
 ALL OTHER DIMENSIONAL TOLERANCES:  
 .X = ±.2  
 .XX = ±.02  
 .XXX = ±.005

APPROVALS	DATE
DRAWN BY R.CARRICK	08/08/2001
CHECKED BY D.PARHAM	08/08/2001
APPROVED BY T.CLARK	08/08/2001

**L-com** Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845

CATEGORY: RACK PANELS

PRODUCT DESCRIPTION: 2U RACK PNL W/32 FC MM CPLR+CMB

SIZE	FSCM NO.	DWG. NO.	REV.
<b>B</b>	<b>43321</b>	<b>PR35FC32CMB</b>	<b>C</b>

SCALE: 1:2 CAD FILE: PR35FC32CMB.SLDRW SHEET 1 OF 1

