




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED TO PRODUCTION	08/08/01	R.CARRICK
B	ECN#2620 UPDATE FORMATS, ADD METRIC DIMENSIONS, UPDATE NOTES	11/08/06	MCCORMICK
C	ECN5376: RE-MODELED AND RE-DIMENSIONED	3/18/11	D.FRISIELLO



- NOTES:
1. MATERIAL: .06 THICK COLD ROLLED STEEL.
 2. PANEL FINISH: FLAT BLACK POWDER COAT.
 3. SILKSCREEN COLOR: WHITE.
 4. PANEL ASSEMBLY SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.
 5. PANEL ASSEMBLY IS SHIPPED WITH DUST CAPS INSTALLED. (NOT SHOWN)

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]
 OVERALL CABLE LENGTH TOLERANCE:
 ≤12 [305] = +1 [25] / -0
 >12 [305] ≤60 [1524] = +2[51] / -0
 >60 [1524] ≤120 [3048] = +4 [102] / -0
 >120 [3048] ≤300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0%
 ALL OTHER DIMENSIONAL TOLERANCES:
 .X = ±.2
 .XX = ±.02
 .XXX = ±.005

APPROVALS	DATE
DRAWN BY R.CARRICK	08/08/2001
CHECKED BY D.PARHAM	08/08/2001
APPROVED BY T.CLARK	08/08/2001

L-com Global Connectivity
 45 BEECHWOOD DRIVE
 NORTH ANDOVER, MA
 01845

CATEGORY RACK PANELS	
PRODUCT DESCRIPTION 2U RACK PNL W/32 ST MM CPLR+CMB	
SIZE B	FSCM NO. 43321
DWG. NO. PR35ST32CMB	REV. C
SCALE: 1:2	CAD FILE: PR35ST32CMB.SLDDRW
SHEET 1 OF 1	