




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/08/2023	SREITER	AGANWANI



RECOMMENDED MOUNTING PAD

NOTES:

ELECTRICAL DATA:

1. IMPEDANCE: 50Ω
2. FREQUENCY RANGE: DC TO 8GHz
3. VSWR: 1.1:1

MECHANICAL:

1. BODY: BRASS, GOLD PLATED
2. CONTACT: BERYLLIUM COPPER, GOLD PLATED
3. INSULATION: PTFE

ALL DIMENSIONS FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [1.3]</p> <p>THIRD-ANGLE PROJECTION</p>	<p>APPROVALS</p> <p>DATE</p>	<p>L-com an INFINITI® brand</p> <p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p>	
	<p>DRAWN BY SREITER</p> <p>CHECKED BY DWANG</p> <p>APPROVED BY AGANWANI</p>		<p>03/08/2023</p> <p>03/30/2023</p> <p>03/30/2023</p>
	<p>CATEGORY</p> <p>PCB CONNECTOR</p>		
	<p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p> <p>COLOR VARIATIONS MAY OCCUR</p>		
<p>PRODUCT DESCRIPTION</p> <p>SMP MALE LIMITED DETENT CONNECTOR SOLDER ATTACHMENT END LAUNCH PCB, UP TO 8 GHz</p>		<p>SIZE</p> <p>A</p>	
<p>SCALE: NONE</p>		<p>CAGE CODE</p> <p>43321</p>	
<p>ITEM NO.</p> <p>RFPCB-SMP-MS-8G-206</p>		<p>REV.</p> <p>A</p>	
<p>CAD FILE: RFPCB-SMP-MS-8G-203.SLDDRW</p>		<p>SHEET 1 OF 1</p>	