


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	11/26/2018	JYOU
B	ECN 9837: REVISE DRAWING DIMENSIONING AND FORMAT	05/02/2019	DFRISIELLO
C	ECN 10047: REVISED 3D MODEL AND DRAWING	07/17/2019	MMARTINEZ



NOTES:
 1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY JYOU	DATE 10/31/2018		50 HIGH STREET NORTH ANDOVER, MA 01845			
	CHECKED BY BGATES	10/31/2018		CATEGORY 19" RACKS			
	APPROVED BY BGATES	10/31/2018	PRODUCT DESCRIPTION L-COM VERTICAL 19" WALL MOUNT RACK 2U	SIZE A	FSCM NO. 43321	DWG. NO. RP00002-2	REV. C
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: RP00002-2.SLDDRW	SHEET 1 OF 1		