



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                                                   |            |            |
|-----------|---------------------------------------------------|------------|------------|
| REV       | DESCRIPTION                                       | DATE       | APPROVED   |
| A         | REV A DRAWING RELEASED                            | 11/27/2018 | JYOU       |
| B         | ECN 9837: REVISED DRAWING DIMENSIONING AND FORMAT | 05/03/2019 | DFRISIELLO |
| C         | ECN 10047: REVISED 3D MODEL AND DRAWING           | 07/17/2019 | MMARTINEZ  |



NOTES:  
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |                                                                                                      |                                                                   |                                                                                                                                              |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| <p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE:<br/> <math>\leq 12</math> [305] = +1 [25] / -0<br/> <math>&gt;12</math> [305] <math>\leq 60</math> [1524] = +2 [51] / -0<br/> <math>&gt;60</math> [1524] <math>\leq 120</math> [3048] = +4 [102] / -0<br/> <math>&gt;120</math> [3048] <math>\leq 300</math> [7620] = +6 [152] / -0<br/> <math>&gt;300</math> [7620] = +5% / -0%</p> <p>ALL OTHER DIMENSIONAL TOLERANCES:<br/> .X = <math>\pm .2</math> [5.08]<br/> .XX = <math>\pm .02</math> [5.1]<br/> .XXX = <math>\pm .005</math> [1.3]</p> <p>PROJECTION<br/> </p> | <p>APPROVALS</p> <p>DRAWN BY<br/>JYOU</p> <p>CHECKED BY<br/>BGATES</p> <p>APPROVED BY<br/>BGATES</p> | <p>DATE</p> <p>11/05/2018</p> <p>11/05/2018</p> <p>11/05/2018</p> | <p><b>L-com</b> Global Connectivity</p> <p>50 HIGH STREET<br/>NORTH ANDOVER, MA<br/>01845</p>                                                |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | <p>CATEGORY</p> <p>19" RACKS</p>                                                                     |                                                                   | <p>PRODUCT DESCRIPTION</p> <p>L-COM OPEN FRAME 19" WALL MOUNT RACK<br/>12" DEPTH - 8U</p>                                                    |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | <p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p> <p>COLOR VARIATIONS MAY OCCUR</p>    |                                                                   | <p>SIZE<br/><b>A</b></p> <p>FSCM NO.<br/><b>43321</b></p> <p>DWG. NO.<br/>RP00015-8</p> <p>SCALE: NONE</p> <p>CAD FILE: RP00015-8.SLDDRW</p> |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | <p>REVISIONS</p> <p>REV. <b>C</b></p>                                                                |                                                                   | <p>SHEET 1 OF 1</p>                                                                                                                          |