


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES SFODST-MT-01-OD1	10/17/14	D. DESJARDIN



PART NUMBER	METERS [FEET]
SFODST-MT-01	1.0 [3.28]
SFODST-MT-02	2.0 [6.56]
SFODST-MT-03	3.0 [9.84]
SFODST-MT-04	4.0 [13.12]
SFODST-MT-05	5.0 [16.40]

- NOTES:**
- CONNECTOR ASSEMBLY POLISH TYPE: PC
 - ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12 [305] = +1 [25] / -0$ $> 12 [305] \leq 60 [1524] = +2 [51] / -0$ $> 60 [1524] \leq 120 [3048] = +4 [102] / -0$ $> 120 [3048] \leq 300 [7620] = +6 [152] / -0$ $> 300 [7620] = +5\% / -0\%$ ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2 [5.08]$ $.XX = \pm .02 [51]$ $.XXX = \pm .005 [1.27]$	APPROVALS DRAWN BY C.MCCORMICK CHECKED BY D.PARHAM APPROVED BY R.CARRICK	DATE 01/07/2004 01/07/2004 01/07/2004	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY FIBER OPTICS	
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. SFODST-MT

SCALE: NONE | CAD FILE: SFODST-MT.SLDDRW | SHEET 1 OF 1