


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES SFOST-01-OD1	6/25/14	D. DESJARDIN



PART NUMBER	LENGTH METERS [FEET]
SFOST-01	1.0 [3.3]
SFOST-02	2.0 [6.6]
SFOST-03	3.0 [9.8]
SFOST-04	4.0 [13.1]
SFOST-05	5.0 [16.4]

- NOTES:**
- CONNECTOR ASSEMBLY POLISH TYPE: PC
  - ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY C.McCORMICK	12/28/00				
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY DFP	01/19/01	CATEGORY FIBER OPTICS			
	APPROVED BY R.CARRICK	01/19/01	PRODUCT DESCRIPTION CA ST-ST 9/125 SIMPLEX			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. SFOST	REV. <b>A</b>
SFOST-01-OD1			SCALE: NONE	CAD FILE: SFOST.SLDDRW	SHEET 1 OF 1	