


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/1/10	D.GRIFFIN




12X, SNAP IN AREA

3X, KNOCKOUT

6.69  
[170.0]

3.94  
[100.0]

1.18  
[30.0]



12X, RJ45 JACK

**SPECIFICATIONS:**

**MATERIAL:**  
HOUSING: HIGH IMPACT FLAME RETARDANT PLASTIC, UL94V-0,  
COLOR: WHITE

**ELECTRICAL:**  
JACK WIRING: 50μ IN OF GOLD OVER 100μ IN OF NICKEL.  
CURRENT RATING: 1.5 AMPS

**MECHANICAL:**  
PLUG INSERTION LIFE: 750 CYCLES MIN.  
TEMPERATURE RANGE: -40°F TO +150°F (-40°C TO 68°C)

**MISCELLANEOUS:**  
CONNECTOR: 110 INSULATION DISPLACEMENT CONNECTOR (IDC)  
ACCEPT 22 - 26 AWG SOLID WIRE AND ARE COLOR CODED FOR  
EIA568A AND B WIRING.

SURFACE BOX IS SUPPLIED WITH BLUE AND RED SNAP-IN ICONS, WRITE  
-IN STRIPS, DOUBLE SIDED ADHESIVE AND WOOD SCREWS.

PACKAGING: COMPONENT AND SUPPLIES SHALL BE INDIVIDUALLY  
PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**RoHS Compliant** ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005  ANGULAR TOLERANCES: ALL = ± 1°	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D.FRISIELLO	9/30/10			
	CHECKED BY C.JEREZ	9/30/10	CATEGORY MODULAR		
	APPROVED BY P.McNEIL	9/30/10	PRODUCT DESCRIPTION SURFACE MOUNT IDC 12 PORT CAT5 JACK		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. SMM45-12W	REV. <b>A</b>
		SCALE: NONE	CAD FILE: SMM45-12W.SLDDRW		SHEET 1 OF 1