


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/1/10	D.GRIFFIN



**SPECIFICATIONS:**

**MATERIAL:**  
 HOUSING: HIGH IMPACT FLAME RETARDANT PLASTIC, UL94V-0,  
 COLOR: WHITE

**ELECTRICAL:**  
 JACK WIRING: 50μ IN OF GOLD OVER 100μ IN OF NICKEL.  
 CURRENT RATING: 1.5 AMPS

**MECHANICAL:**  
 PLUG INSERTION LIFE: 750 CYCLES MIN.  
 TEMPERATURE RANGE: -40°F TO +150°F (-40°C TO 68°C)

**MISCELLANEOUS:**  
 CONNECTOR: 110 INSULATION DISPLACEMENT CONNECTOR (IDC)  
 ACCEPT 22 - 26 AWG SOLID WIRE AND ARE COLOR CODED FOR  
 EIA568A AND B WIRING.

SURFACE BOX IS SUPPLIED WITH BLUE AND RED SNAP-IN ICONS, WRITE  
 -IN STRIPS, DOUBLE SIDED ADHESIVE AND WOOD SCREWS.

PACKAGING: COMPONENT AND SUPPLIES SHALL BE INDIVIDUALLY  
 PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**RoHS Compliant** ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005  ANGULAR TOLERANCES: ALL = ± 1°	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D.FRISIELLO	9/30/10			
	CHECKED BY C.JEREZ	9/30/10	CATEGORY MODULAR		
	APPROVED BY P.McNEIL	9/30/10	PRODUCT DESCRIPTION 6 PORT CAT 5 SURFACE MOUNT JACK		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. SMM45-6W	REV. <b>A</b>
SCALE: NONE		CAD FILE: SMM45-6W.SLDRW		SHEET 1 OF 1	