


Bulk Cable Specification

Cross-Sectional View 		Color Code 1. White 2. Black 3. Red 4. Green 5. Yellow 6. Blue
ITEM		DESCRIPTION
Conductor	No. of Conductors	6
	Material	Bare Copper
	Construction	26 AWG Stranded (7x34)
Insulation	Material	Polypropylene
	Nominal Diameter	0.037" [0.95±0.05mm]
	Thickness	0.008" [0.21mm] Minimum
Shielding	Material	N/A
	Coverage	N/A
Drain Wire	Material	N/A
	Construction	N/A
Braiding	Material	N/A
	Coverage	N/A
Jacket	Material	PVC
	Thickness	0.02" [0.51mm] Minimum
	Nominal Diameter	Oval
	Color	Silver Satin
ELECTRICAL PROPERTIES		
Conductor Resistance	N/A	
Insulation Resistance	N/A	
Impedance	N/A	
Maximum Voltage	150V	
Maximum Current Rating	N/A	
LISTINGS / RATINGS		
RoHS Compliant	Yes	
Flammability Rating	FT2	
UL Style	20251	
MISCELLANEOUS		
Operating Temperature	-10 to +60°C	
Storage Temperature	-10 to +60°C	
Minimum Bending Radius	N/A	
Packaging	100 FT: Coil with Stretch Wrap in accordance with L-com specification PS-0031 500 FT: Reel with Stretch Wrap 1000 FT: Reel with Stretch Wrap	