


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
G	ECN6669: CN RELEASE. UPD FORMAT/PKG.	8/27/13	D. DESJARDIN
H	ECN 7055: CATEGORY 3 CABLE NOTE WAS CATEGORY 5E	9/11/13	D. DESJARDIN
J	ECN 7149: REVISED OVERALL LENGTH TO END-TO-END	11/12/13	D. FRISIELLO



PART NUMBER	LENGTH FEET [METERS]
TDC350MM-5	5.0 [1.52]
TDC350MM-10	10.0 [3.05]
TDC350MM-15	15.0 [4.57]
TDC350MM-25	25.0 [7.62]
TDC350MM-50	50.0 [15.24]
TDC350MM-100	100.0 [30.48]

**NOTES:**

- SEE SHEET 2 FOR WIRING MAP.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.


**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	APPROVALS DRAWN BY C.MCCORMICK CHECKED BY ENG APPROVED BY R.CARRICK	DATE 09/21/2001 09/21/2001 09/21/2001	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY <b>TELECOM/MODULAR</b>
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
			DWG. NO. <b>TDC350MM</b>	REV. <b>J</b>
		SCALE: NONE	CAD FILE: TDC350MM.SLDDRW	
		SHEET 1 OF 2		

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

WIRING MAP

PAIR	"P1"	COLOR	"P2"	PAIR	"P1"	COLOR	"P2"
1	1	BLUE/WHITE	1	14	14	BROWN/BLACK	14
	26	WHITE/BLUE	26		39	BLACK/BROWN	39
2	2	ORANGE/WHITE	2	15	15	GRAY/BLACK	15
	27	WHITE/ORANGE	27		40	BLACK/GRAY	40
3	3	GREEN/WHITE	3	16	16	BLUE/YELLOW	16
	28	WHITE/GREEN	28		41	YELLOW/BLUE	41
4	4	BROWN/WHITE	4	17	17	ORANGE/YELLOW	17
	29	WHITE/BROWN	29		42	YELLOW/ORANGE	42
5	5	GRAY/WHITE	5	18	18	GREEN/YELLOW	18
	30	WHITE/GRAY	30		43	YELLOW/GREEN	43
6	6	BLUE/RED	6	19	19	BROWN/YELLOW	19
	31	RED/BLUE	31		44	YELLOW/BROWN	44
7	7	ORANGE/RED	7	20	20	GRAY/YELLOW	20
	32	RED/ORANGE	32		45	YELLOW/GRAY	45
8	8	GREEN/RED	8	21	21	BLUE/VIOLET	21
	33	RED/GREEN	33		46	VIOLET/BLUE	46
9	9	BROWN/RED	9	22	22	ORANGE/VIOLET	22
	34	RED/BROWN	34		47	VIOLET/ORANGE	47
10	10	GRAY/RED	10	23	23	GREEN/VIOLET	23
	35	RED/GRAY	35		48	VIOLET/GREEN	48
11	11	BLUE/BLACK	11	24	24	BROWN/VIOLET	24
	36	BLACK/BLUE	36		49	VIOLET/BROWN	49
12	12	ORANGE/BLACK	12	25	25	GRAY/VIOLET	25
	37	BLACK/ORANGE	37		50	VIOLET/GRAY	50
13	13	GREEN/BLACK	13				
	38	BLACK/GREEN	38				

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION CABLE CAT 3 CN50 M/M			
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. TDC350MM	REV. <b>J</b>
SCALE: NONE		CAD FILE: TDC350MM.SLDDRW	
			SHEET 2 OF 2