

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES TDC550MM-5-OD1 AT REV C	11/13/14	D. CASTRO

WIRE MAP					
"P1"	PAIR	"P2"	"P1"	PAIR	"P2"
1	1	1	14	14	14
26	1	26	39	14	39
2	2	2	15	15	15
27	2	27	40	15	40
3	3	3	16	16	16
28	3	28	41	16	41
4	4	4	17	17	17
29	4	29	42	17	42
5	5	5	18	18	18
30	5	30	43	18	43
6	6	6	19	19	19
31	6	31	44	19	44
7	7	7	20	20	20
32	7	32	45	20	45
8	8	8	21	21	21
33	8	33	46	21	46
9	9	9	22	22	22
34	9	34	47	22	47
10	10	10	23	23	23
35	10	35	48	23	48
11	11	11	24	24	24
36	11	36	49	24	49
12	12	12	25	25	25
37	12	37	50	25	50
13	13	13			
38	13	38			




TABLE A	
MODEL	LENGTH FEET [METERS]
TDC550MM-5	5.0 [1.52]
TDC550MM-10	10.0 [3.05]
TDC550MM-15	15.0 [4.57]
TDC550MM-25	25.0 [7.62]
TDC550MM-50	50.0 [15.24]
TDC550MM-100	100.0 [30.48]

NOTES:

1. CABLE ASSEMBLY IS CATEGORY 5 RATED.
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY D PARHAM	7/26/2001				
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	CHECKED BY T CLARK	7/26/2001	CATEGORY TELECOM/MODULAR			
	APPROVED BY R CARRICK	7/31/2001	PRODUCT DESCRIPTION CABLE CAT5 CN50 M/M 180DEG			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TDC550MM	REV. A
			SCALE: NONE	CAD FILE: TDC550MM.SLDDRW	SHEET 1 OF 1	