


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/29/13	D.GRIFFIN



NOTES:

MATERIAL:
 COUPLER HOUSING: POLYCARBONATE RESIN HIGH-IMPACT
 UL94V-0 THERMOPLASTIC. COLOR, WHITE
 CONTACTS: PHOSPHOR BRONZE, 50 μINCHES GOLD PLATE.

ELECTRICAL:
 DC CURRENT RATING: 1.5 AMPS
 DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS AC.

MISCELLANEOUS:
 OPERATING TEMPERATURE RANGE: -10°C TO +60°C
 APPLICATION: CATEGORY 6.
 WIRING: STRAIGHT THROUGH.
 PANEL THICKNESS: .065" [1.65mm] MAX.
 ALL DIMENSIONS ARE FOR REFERENCE ONLY.

PACKAGING:
 COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13]	APPROVALS DRAWN BY D.FRISIELLO	DATE 10/23/13	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	CHECKED BY D.GUITADAURO	DATE 10/23/13		CATEGORY TELECOM/MODULAR		
	APPROVED BY D. GALLAGHER	DATE 10/23/13	PRODUCT DESCRIPTION C6A 90° KEYSTONE CPLR			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TDG1026K-RC6A
SCALE: NONE		CAD FILE: TDG1026K-RC6A.SLDDRW		SHEET 1 OF 1		