






8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/23/15	D.GRIFFIN



FOUR TWISTED PAIRS, CATEGORY 6A
26AWG STRANDED TINNED COPPER WITH ALUMINUM/POLYESTER FOIL SHIELDING AND TINNED COPPER BRAID SHIELD
JACKET: HIGH FLEX, THERMOPLASTIC ELASTOMER
COLOR: TEAL



TMD24 015 015 053

{
XXXM LENGTH IN METERS
XXXF LENGTH IN FEET

- NOTES:**
1. PLUG CONFORMS TO TIA-1096
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
- REGULATORY COMPLIANCE:**
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [.51] .XXX = ±.005 [.13]	APPROVALS DRAWN BY D.FRISIELLO	DATE 9/23/15	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CHECKED BY D.GUITADAURO	DATE 9/23/15		CATEGORY TELECOM/MODULAR	
	APPROVED BY D.GALLGHER	DATE 9/23/15	PRODUCT DESCRIPTION RJ45 C6A SF/UTP HFO TEAL		
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TMD24015015053

SCALE: NONE | CAD FILE: TMD24015015053.SLDDRW | SHEET 1 OF 1