



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/21/2016	DFRISIELLO
B	ECN 8696: ADD P/NS -1,-3 AND -75; ADD FALME RATING	03/28/2017	SLI
C	ECN 9520: NEW CONNECTOR, REMOVE SHRINK TUBE, ROHS STAMP	11/14/2018	DFRISIELLO



MODEL NUMBER	LENGTH	
	FEET	METERS
TRD695AOD-1	1.0	0.30
TRD695AOD-3	3.0	0.91
TRD695AOD-5	5.0	1.52
TRD695AOD-10	10.0	3.05
TRD695AOD-25	25.0	7.62
TRD695AOD-50	50.0	15.24
TRD695AOD-75	75.0	22.86
TRD695AOD-100	100.0	30.48



NOTES:

MATERIAL:

PLUG HOUSING: POLYCARBONATE, CLEAR, UL94V-0
 CONTACTS: PHOSPHOR BRONZE.
 CABLE JACKET: LINEAR LOW-DENSITY POLYETHYLENE, BLACK, (LLDPE)

FINISH:

CONTACTS: 50 μINCHES GOLD IN CONTACT AREA
 OVER 100 μINCHES NICKEL PLATE OVERALL.

CABLE CHARACTERISTICS:

CAT 6A, CMX, UNSHIELDED FOUR TWISTED PAIRS MODULAR CORD,
 23 AWG SOLID BARE COPPER CONDUCTORS
 OUTER JACKET: UV RESISTANT, OUTDOOR JACKET.
 FLAME RATING: IEC-332-1, UL: CMX

MISCELLANEOUS:

LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
 OPERATING TEMPERATURE RANGE: -20°C TO +70°C.
 CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY DFRISIELLO	10/04/2016	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY D.DESJARDIN	10/04/2016	CATEGORY TELECOM/MODULAR
	APPROVED BY DGUTTADAUR	10/21/2016	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION RJ45 C6A UTP 23SLD LLDPE BLK CMX OTR	
COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TRD695AOD
	SCALE: NONE	CAD FILE: TRD695AOD.SLDDRW	REV. C
			SHEET 1 OF 1