







THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|--------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 7/9/14 | D.GRIFFIN |
| | | | |
| | | | |



2X SHIELDED RJ45 MODULAR PLUG
GOLD PLATED CONTACTS
(8P8C)




LENGTH
SEE SHEET 2

- NOTES:**
1. PLUG CONFORMS TO TIA-1096.
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.
- REGULATORY COMPLIANCE:**
CE2011/65/EU (RoHS DIRECTIVE)

| | | | | |
|---|-----------------------------|----------|--|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% | APPROVALS | DATE | | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 |
| | DRAWN BY D. DESJARDIN | 10/17/13 | | CATEGORY TELECOM/MODULAR |
| ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13] | CHECKED BY D. FRISIELLO | 7/8/14 | PRODUCT DESCRIPTION C5E PVC FTP STAK-UP | |
| PROJECTION | APPROVED BY D. GALLAGHER | 7/8/14 | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | SCALE: NONE |
| | COLOR VARIATIONS MAY OCCUR | | SIZE A | FSCM NO. 43321 |
| | | | DWG. NO. TRD815SRA15 | REV. A |
| | | | CAD FILE: TRD815SRA15.SLDDRW | |
| | | | SHEET 1 OF 2 | |

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| PART NUMBER | COLOR | LENGTH FEET [METERS] | PART NUMBER | COLOR | LENGTH FEET [METERS] |
|-------------------|-------|----------------------|-------------------|-------|----------------------|
| TRD815SRA15BLK-1 | BLACK | 1.0 [0.30] | TRD815SRA15RED-1 | RED | 1.0 [0.30] |
| TRD815SRA15BLK-3 | BLACK | 3.0 [0.91] | TRD815SRA15RED-3 | RED | 3.0 [0.91] |
| TRD815SRA15BLK-5 | BLACK | 5.0 [1.52] | TRD815SRA15RED-5 | RED | 5.0 [1.52] |
| TRD815SRA15BLK-7 | BLACK | 7.0 [2.13] | TRD815SRA15RED-7 | RED | 7.0 [2.13] |
| TRD815SRA15BLK-10 | BLACK | 10.0 [3.05] | TRD815SRA15RED-10 | RED | 10.0 [3.05] |
| | | | | | |
| TRD815SRA15BLU-1 | BLUE | 1.0 [0.30] | TRD815SRA15GRY-1 | GRAY | 1.0 [0.30] |
| TRD815SRA15BLU-3 | BLUE | 3.0 [0.91] | TRD815SRA15GRY-3 | GRAY | 3.0 [0.91] |
| TRD815SRA15BLU-5 | BLUE | 5.0 [1.52] | TRD815SRA15GRY-5 | GRAY | 5.0 [1.52] |
| TRD815SRA15BLU-7 | BLUE | 7.0 [2.13] | TRD815SRA15GRY-7 | GRAY | 7.0 [2.13] |
| TRD815SRA15BLU-10 | BLUE | 10.0 [3.05] | TRD815SRA15GRY-10 | GRAY | 10.0 [3.05] |

| | | | |
|---|--------------------------|--|------------------|
|  | | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | |
| CATEGORY | | | |
| TELECOM/MODULAR | | | |
| PRODUCT DESCRIPTION | | | |
| C5E PVC FTP STAK-UP | | | |
| SIZE A | FSCM NO. 43321 | DWG. NO. TRD815SRA15 | REV. A |
| SCALE: NONE | | CAD FILE: TRD815SRA15.SLDDRW | |
| | | | SHEET 2 OF 2 |