

6

5

4


3

2


1

## REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	11/04/2024	DMAY	DGUTTADAURO



C1



M12\*1.0

CABLE


## NOTES:

- QC IMPORTANT DIMENSION.
- WATERPROOF RATE: IP68, MATED 1m/24h  
IP69K, MATED
- C1:
  - HOUSING: THERMOPLASTIC, BLACK
  - PIN: COPPER ALLOY, GOLD PLATED
  - NUT: METAL
  - OUTER MOLD: THERMOPLASTIC, BLACK
- CABLE: UL20233, 14AWG\*5C  
PU JACKET, OD=10.2mm, BLACK
- TEMPERATURE RANGE: -20°C TO +80°C
- OPERATING VOLTAGE: 630V
- NOMINAL CURRENT: 16A

REGULATORY COMPLIANCE:  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

PIN OUT	
C1	WIRE COLOR
1	BROWN
2	WHITE
3	BLUE
4	BLACK
FE	GRAY



C1  
PIN ASSIGNMENT  
FRONT VIEW

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS


TOLERANCES:  
X = ±2 [5] | FRACTIONS  
XX = ±0.02 [0.5] | ± 1/32  
.XXX = ±0.005 [0.13] | ANGLES ± 1°

CABLE LENGTH TOLERANCES:  
≤12 [305] = +1 [25] / -0  
>12 [305] ≤ 60 [1524] = +2 [51] / -0  
>60 [1524] ≤ 120 [3048] = +4 [102] / -0  
>120 [3048] ≤ 300 [7620] = +6 [152] / -0  
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE.  
UN-DIMENSIONED NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**  
an INFINIT@ brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

SCALE	SHEET
NONE	1 OF 1

DESCRIPTION  
M12 DC POWER CABLE ASSEMBLY, 5 POSITION L CODE, IP68  
IP69K, MALE TO OPEN, 14AWG, 63V, 16A, UL 20233 PU JACKET,  
BLACK, 1M

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DMAY	TRGL504-P4B-1M	A

6

5

4

3

2

1