


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/1/10	D.GRIFFIN
B	ECN 4905: CLARIFY PIN 1 AND ADD DIELECTRIC CALL OUT	7/14/10	D.FRISIELLO
C	ECN 7063: REMOVED 3.0 REQUIREMENTS NOTE. UPDATED FORMAT AND ROHS.	9/16/13	D. DESJARDIN



WIRING MAP	
"J1"	"P1"
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
SHELL	SHELL

NOTES:

MATERIAL:
 HOUSING: PVC, BLUE (PANTONE 300C)
 INSULATOR: LCP (BLUE)
 CONTACTS: BRASS

FINISH:
 CONTACTS: GOLD PLATING OVER NICKEL PLATE
 SHELL: NICKEL SILVER PLATING

MISCELLANEOUS:
 ALL DIMENSIONS ARE FOR REFERENCE ONLY.
 COMPONENT SHALL BE TESTED FOR CONTINUITY.
 COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 ROHS, CE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	3/30/10		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY M.MARTINEZ	3/30/10	PRODUCT DESCRIPTION ADPTR USB 3.0 TYPE A M/F	
	APPROVED BY S.SMITH	3/30/10		
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		DWG. NO. UAD035MF	REV. C
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: UAD035MF.SLDDRW	SHEET 1 OF 1