


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|--------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 8/3/11 | D.GRIFFIN |
| | | | |
| | | | |



RoHS Compliant ✓

NOTE

1. MATERIAL: .06" [1.52] THK COLD ROLLED STEEL
2. FINISH: FLAT BLACK POWDER COAT
3. COUPLER SHIPPED WITH DUST CAPS INSTALLED. (NOT SHOWN)
4. PACKAGE IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.

| | | | | |
|---|--|----------------------------|--|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% | APPROVALS | DATE | | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 |
| | DRAWN BY D. PARHAM | 08/02/2011 | | |
| ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 | CHECKED BY D. CASTRO | 08/02/2011 | CATEGORY RACK PANELS | |
| | APPROVED BY M. MARTINEZ | 08/02/2011 | PRODUCT DESCRIPTION 3.5"X19"PNL /24 ST SMX CPL BLK | |
| PROJECTION | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | COLOR VARIATIONS MAY OCCUR | SIZE A | FSCM NO. 43321 |
| | | | DWG. NO. UPR35-24STB | REV. A |
| | | | SCALE: NONE | CAD FILE: UPR35-24STB.SLDDRW |
| | | | | SHEET 1 OF 1 |