



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES WPHD15CA-OD1 AT REV B	12/2/14	D. CASTRO

WIRE MAP		
PIN	SIGNAL	WIRE
1	RED	COAX CC
2	GREEN	COAX CC
3	BLUE	COAX CC
4	ID BIT 2	TP 1
5	GROUND	TP 1
6	RED SHIELD	COAX SHLD
7	GREEN SHIELD	COAX SHLD
8	BLUE SHIELD	COAX SHLD
9	DDV +5V	COND 1
10	SYNC RTN	TP 3/4
11	ID BIT 0	TP 2
12	ID BIT 1	TP 2
13	HORZ SYNC	COND 2
14	VER SYNC	TP 3
15	ID BIT 3	TP 4
16	SHELL	DRAIN WIRE



J1  
SVGA HD15 JACK  
FIELD TERMINATION  
w/ FEMALE, 15-CONTACT  
HIGH DENSITY D-SUB CONN  
AND 2X 8-POS TERMINAL BLOCKS

NOTES:  
1. MATERIAL: STAINLESS STEEL  
2. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY B.MAZEJKA	09/22/2003		CATEGORY <b>AUDIO/VIDEO</b>
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY D.PARHAM	09/26/2003	PRODUCT DESCRIPTION <b>WALLPLATE ASSEMBLY HD15 FEM</b>	
PROJECTION 	APPROVED BY C.McCORMICK	09/26/2003	SIZE <b>A</b>	FSCM NO. <b>43321</b>
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		DWG. NO. WPHD15FT	REV. <b>A</b>
	COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: WPHD15FT.SLDDRW
			SHEET 1 OF 1	